

Packing Instruction 650

Primary Leak-proof receptacle (*sift proof for solids*) i.e. sample tube. Multiple primary receptacles within a single secondary container must be individually wrapped or separated to prevent contact between them.

Leak-proof secondary container that satisfies 95kPa pressure test. Maximum volume 4 Litres in total (4Kg solid).

Absorbent material between primary receptacle(s) and secondary container (not required for solid samples). Must be sufficient to absorb contents of the primary receptacle(s).

Unspecified cushioning material to secure the secondary packaging within the outer packaging

The nature of the outer packaging is not specified but must be of adequate strength for its capacity, weight and intended use. For transport, the outer packaging should be marked externally with the symbol shown in **Figure 1** below.

Itemised list of contents to be enclosed between secondary container and outer packaging.

Packages consigned as freight must be at least 100mm in the smallest dimension.

Name, address and telephone number of a responsible person (Sender).

Figure 1. Hazard label



The completed package shall be capable of withstanding a drop test of not less than 1.2 m.